

Thank you for purchasing our bike U lock. For your better use of this bike lock, please read this user manual carefully. If you have any problems when using this bicycle lock, just feel free to contact with us at **support@ubullox.com**. Contact us with your order ID, we will respond to you within 24 hours and help you solve the problem. We cover all the products with 30 days free replacement or refund and 1 year warranty. **(Except human damage)**

- **Package List**

1* U Lock

1* 120cm/4feet Steel Cable

3* Keys

1* Mounting Bracket

- **Notice**

1.Please keep the lock cylinder clean and dry during daily use.

2.If the lock is difficult to open because of sediment or long time of not using, some pencil lead powder can be added to solve this problem.

3.Never leave your bike in remote places or leave your bike unattended for a long time.

• Main Functions


- 1.U lock is made of high-quality alloy steel material which is heat resistant and hydraulic shear resistant.
- 2.U lock is wrapped with environmentally-friendly silicone rubber which is comfortable and not harmful to people.
- 3.Comes with 120cm/4feet long steel cable which allows you to lock not only the frame, but also both wheels.

• Dimensions

Length:145mm/5.71 inch


Width:65mm/2.56inch

Diameter:16mm/0.63inch




3 Keys

Material: rust-resistant
pure copper




Length:120cm/4feet




Notice: The length of the cable
may have a certain amount of error.





Suitable for all circular
tripod in
diameter $\leq 30\text{mm}/1.18\text{inch}$



• Installation





D



① Firstly, install the mounting bracket(A) on the seatpost(B).


② Next, push the lock-body (C) into the mounting bracket.



③ Then, insert the locking beam(D) into the lock-body(C). Finish installation.

④ The mounting bracket is suitable for all circular tripod in diameter $\leq 30\text{mm}$

• U Lock USE



• Lock+ Cable Use

